

**NOTES:**

- A. MATERIAL & FINISH:  
HANDLE - SEE PART NUMBER -EE  
BASE - SEE PART NUMBER -EE  
BUSHING - NYLON, NATURAL  
ROLL PIN - 300 SERIES STAINLESS STEEL, PASSIVATED  
HEX NUT & LOCK WASHER - 300 SERIES STAINLESS STEEL, NATURAL
- B. COSMETIC SPECIFICATION:  
ALL SURFACES UNLESS OTHERWISE NOTED ARE TO CONFORM TO A CLASS \*B\* DESIGNATION AS DESCRIBED IN SOUTHCO COSMETIC SPECIFICATION S-121-03.
- C. PACKAGING: PULLS ARE PACKAGED IN A TRAY, LAYERED. FOR INDIVIDUALLY PACKAGED, (1) HANDLE IN POLYETHYLENE BAG, REMOVE THE -3 SUFFIX IN THE PART No.
- D. ALL HANDLES ARE RoHS COMPLIANT.
- E. TO REQUEST A THREAD SIZE NOT LISTED CONSULT SOUTHCO ENGINEERING.

**southco**

PROPRIETARY ITEM - EXCEPT FOR USES EXPRESSLY GRANTED IN WRITING INFORMATION DISCLOSED HEREON IS CONFIDENTIAL AND ALL RIGHTS PATENT AND OTHERWISE ARE RESERVED BY SOUTHCO, INC.

P9 FOLDING (INFINITE POSITION) HANDLES


DATE	DRAWN	CHKD	SCALE	DRAWING NUMBER
11SEP2004	DLH		.5:1	J-P9-1

REV	DATE	DRAWN/CHKD	DESCRIPTION
A	17FEB2006	DLH	RELEASED FOR PRODUCTION
B	09JUL2007	DLH/AJH	PRN: P2007-0881
C	02OCT2007	GDW/JSS	PRN: P2007-1232

PART NUMBER:

P9- AAA - BB - CCD - EE -3

**MILLIMETERS**  
ALL DIMENSIONS WITHOUT TOLERANCES ARE FOR REFERENCE ONLY.



A3 PAPER SIZE

LENGTH BETWEEN MOUNTING HOLES IN MILLIMETERS  
040 = 40mm  
064 = 64mm  
096 = 96mm  
128 = 128mm




HEIGHT OF PULL IN MILLIMETERS  
40 = 40

THREAD TYPE
04 = 4-40 THREAD
06 = 6-32 THREAD
08 = 8-32 THREAD
M3 = M3 x 0.5 THREAD
M4 = M4 x 0.7 THREAD


- 11 = ALUMINUM, CLEAR ANODIZED
- 15 = ALUMINUM, BLACK ANODIZED
- 21 = STEEL, BRIGHT CHROME
- 24 = STAINLESS STEEL, NATURAL

**N - INTERNAL THREADED**

MOUNTING SCREW LENGTH = PANEL THICKNESS + 5mm  
MOUNTING SCREWS NOT INCLUDED



N = FOR INTERNAL THREADS  
X = FOR EXTERNAL THREADS



PANEL PREPARATION  
SCALE 1:1

**X - EXTERNAL THREADED**

PANEL THICKNESS = 8.5 MAX  
MOUNTING HARDWARE INCLUDED - (2) HEX NUTS, (2) LOCKWASHERS

